

Архангельск (8182)63-90-72
Астана (7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06

Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16

Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13

Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93

Киргизия (996)312-96-26-47

Россия (495)268-04-70

Казахстан (772)734-952-31

<https://optosky.nt-rt.ru/> || otp@nt-rt.ru

Лучший миниатюрный УФ-спектрометр



- ATP1010 provides UV, Vis Nir from 185nm to 1100nm, CMOS detector technology from Hamamatsu corporation.
- ATP1010 provides the most advanced spectroscopy technology leading the global best UV range miniature spectrometer.
- ATP1010 is based on very high sensitivity, response rate, high performance, dynamic range, signal to noise, and optical resolution, which are suitable to various industrial applications.
- ATP1010 is designed to fiber optics and light source, the spectra software shows absorbance, transmission and spectrum in real time.
- ATP1010 save 30% cost to integrate to high volume OEM analytical devices.
- ATP1010 is based on 20 years designs expert in spectroscopy technology providing good reproducibility which ensure reproducibility from units unit and lots a lot, which's very important for high volume manufacturers.
- The ATP1010 can receive optical fiber input or free-space input light from the SMA905 interface, measure it according to the set integration time, and output the measurement result via USB2.0 (high speed) or UART.
- ATP1010 OEM spectrometer can get free SDK for spectrometer developer's kit, communication protocol, say C++, C#, Labview and Linux system SDK.

OPTICAL PARAMETER

Spectral Range	0.2-5 nm (Slit size & spectral range)
Focal Distance	28 mm for incidence / 28 mm for output
Dynamic Range	10000 : 1
SNR	> 450:1

OPTICAL PARAMETER

Optical Design	F/4 Crossed C-T
----------------	-----------------

DETECTOR

Detector Type	Linear CMOS
Spectral Range	180-1100 nm Customize
Effective Pixels	512
Sensitivity	1300V/(lx-s)
Dark Noise	13RMS@13°C
Pixel Size	14 × 200 μm

PHYSICAL PARAMETERS

Dimension	45×42×23 mm3
Weight	60g

ELECTRICAL PARAMETER

ADC Depth	16 bit
Power Supply	DC 4.5 5.5 V (type @5V)
Working Humidity	< 90%RH
Integration Time	0.1 ms ~ 10 min
Operating Current	<200 mA
Storage Temperature	-20°C to +70°C
Operating Temperature	-10°C to +50°C

Архангельск (8182)63-90-72 Астана (7172)727-132 Астрахань (8512)99-46-04 Барнаул (3852)73-04-60 Белгород (4722)40-23-64 Брянск (4832)59-03-52 Владивосток (423)249-28-31 Волгоград (844)278-03-48 Вологда (8172)26-41-59 Воронеж (473)204-51-73 Екатеринбург (343)384-55-89 Иваново (4932)77-34-06	Ижевск (3412)26-03-58 Иркутск (395)279-98-46 Казань (843)206-01-48 Калининград (4012)72-03-81 Калуга (4842)92-23-67 Кемерово (3842)65-04-62 Киров (8332)68-02-04 Краснодар (861)203-40-90 Красноярск (391)204-63-61 Курск (4712)77-13-04 Липецк (4742)52-20-81	Магнитогорск (3519)55-03-13 Москва (495)268-04-70 Мурманск (8152)59-64-93 Набережные Челны (8552)20-53-41 Нижний Новгород (831)429-08-12 Новокузнецк (3843)20-46-81 Новосибирск (383)227-86-73 Омск (3812)21-46-40 Орел (4862)44-53-42 Оренбург (3532)37-68-04 Пенза (8412)22-31-16	Пермь (342)205-81-47 Ростов-на-Дону (863)308-18-15 Рязань (4912)46-61-64 Самара (846)206-03-16 Санкт-Петербург (812)309-46-40 Саратов (845)249-38-78 Севастополь (8692)22-31-93 Симферополь (3652)67-13-56 Смоленск (4812)29-41-54 Сочи (862)225-72-31 Ставрополь (8652)20-65-13	Сургут (3462)77-98-35 Тверь (4822)63-31-35 Томск (3822)98-41-53 Тула (4872)74-02-29 Тюмень (3452)66-21-18 Ульяновск (8422)24-23-59 Уфа (347)229-48-12 Хабаровск (4212)92-98-04 Челябинск (351)202-03-61 Череповец (8202)49-02-64 Ярославль (4852)69-52-93
Киргизия (996)312-96-26-47	Россия (495)268-04-70	Казахстан (772)734-952-31		